
Canon

250 MP Ultra High Resolution CMOS Sensor

Product Sheet



Ultra High Resolution and High Speed

Canon LI8020SA CMOS sensor minimizes noise without sacrificing speed by sharing floating diffusion capacitance between multiple pixels, resulting in shrunken readout circuitry and larger photodiode sizes. Progressive reading of small 1.5µm pixels occurs across 16 digital output channels to handle the enormous amount of image data created by roughly 250 million effective pixels. At full resolution, the LI8020SA CMOS sensor achieves a fast frame rate of 5 FPS. With single Region of Interest (ROI) windowing, faster frame rates can be achieved through reduced resolution, creating flexibility in performance.




| • | Reference Standard | Effective Pixel Rows | Max Frame Rate |
|---|-----------------------|-------------------------|-------------------|
| | All Pixels | 12588 | 5 |
| | 8K | 4320 | 24 |
| | 4K | 2160 | 30 |
| | FHD | 1080 | 60 |

Readout Position and Frame Rate Control

The readout start position can be specified to allow flexibility in both frame rate and resolution depending on the application and required performance level. This feature allows the selection of a region of interest scalable to the final application requirements.

Evaluation Kit Available

The Canon LI8020SA Evaluation Kit allows integrators and end users to assess sensor performance and provides assets for image system designers to help accelerate development time. The Evaluation Kit features a camera with a pre-installed LI8020 CMOS sensor with raw data serial output via a CoaXPress interface. The evaluation kit has an open architecture design and gives developers the option to embed processing and software with the on-board FPGA.





250 MP Ultra High Resolution CMOS Sensor

Product Sheet

Specifications

| | LI8020SAC | LI8020SAM |
|--|---------------------------------------|------------|
| Filter Type | RGB | Monochrome |
| Sensitivity (e/lx/sec) | 4,600 | 11,000 |
| Sensor Size | 29.35 mm x 18.88 mm | |
| Number of Effective Pixels | 19568 x 12588 (Horizontal x Vertical) | |
| Pixel Size | 1.5µm x 1.5µm | |
| Scan Type | Progressive Scan | |
| Shutter | Rolling Shutter | |
| Maximum Frame Rate (All Pixels) | Maximum Frame Rate (All Pixels) 5 fps | |
| Register Control Type | Serial Communication | |
| Package Type | 228pin ceramic QFP | |
| Saturation | 5,400 e | |
| Region Of Interest | Yes (one) | |
| Vertically sub-sampling | 1/1, 1/3, 1/5, 1/7, and 1/9 | |
| Dark Random Noise (Room Temp) | 3.8 e- rms @ gain 12dB | |
| Dark Current | 13 e/sec @ 60°C | |
| Drive Frequency | 81 MHz | |
| Output Channels | Data 16 lanes, Clock 4 lanes | |
| Output Format | 810 Mbps @ 10 bit, 972 Mbps @ 12bit | |
| Analog Gains | (-6 dB), 0 dB, 6 dB, 12 dB | |
| Power Consumption | 2.0 W | |
| Power Supply Voltage | 1.2 V, 3.3 V and 3.5 V | |
| Package Size (External Electrodes Not Included) | 43.7 mm x 36.4 mm x 3.97 mm | |

LI8020 Evaluation Kit

Color Filter Options Monochrome / RGB

FPGA Intel Arria 10

PC Interface CoaXPress 1.1 / GeniCAM

Bit Depth / Frame Rate 10 bit, 12 bit / 5 fps

Lens Mount M48 (Lens Not Included)
Features ROI, Exposure Control,


Frame Rate Control,


Bad Pixel Replacement

Windows Software available for download

Please contact our representative for 2 weeks Free Loaner!

Quantum Efficiency Plot





FUNCTIONAL BLOCK DIAGRAM

